SALAMI AND CHEESE MATURATION CABINET



OPERATING TEMPERATURE: +2°C +25°C

KLIMA AGING. PREMIER Control, glass door, glass back, black





MODEL	DIMENSIONS	DESCRIPTION	POWER	CAPACITY KG
KASD900PVB	920x800x2115h	Glass door and glass back	KW 1,05	min/max 50/80Kg*
- provided with no.1 KIT SALAMI included in the price. Cod. 3A90KIT SA - 3 meat hanging frames of 48 teeth + 3 pairs s/s rails** - first level phone assistance for installation included				
KASD1500PVB	1460x850x2115h	Glass door and glass back	KW 1,80	min/max 80/140Kg*
•	KIT SALAMI included in th sistance for installation inc	•	- 6 meat hanging fra	mes of 36 teeth + 6 pairs s/s rails**

[·]

Standard equipment:

- Test centre function
- Tropicalised and customized climate class 5 refrigerant group (2 independent groups on 1500 models) with Gas R290
- 7" touch screen display with icons
- White led lights
- Internal air speed variation
- Horizontal and vertical air flow «patented»
- Automatic air change
- Dehumidifica on
- Heating

- Humidity and temperature probe
- USB door + micro SD
- Datalogger for HACCP
- 20 preset and customizable recipes
- Possibility to set 20 phases per each recipe
- Temperature humidity and electrical power supply alarm management
- Preconfiguresed for direct discharge of evaporator condensation water
- Phone assistance for correct installtion of the machine and training on the basic use of the panel control (phone date to be agreed in advance)

EQUIPMENT AVAILABLE ON REQUEST

For each KLIMA AGING the CHEESE KIT is standard - SALAMI KIT can be substituted, but must must be specified with order.

For KLIMA AGING PREMIER 900 - CHEESE KIT cod. 4M90KIT CA - 4 s/s fridge racks + 4 pairs s/s rails

SALAMI KITI cod. **3A90KIT SA** - 3 meat hanging frames of 48 teeth + 3 pairs s/s rails

For KLIMA AGING PREMIER 1500 CHEESE KIT cod. 8M150KIT CA - 8 s/s fridge racks + 8 pairs s/s rails

SALAMI KIT cod. 6A150KIT SA - 6 meat hanging frames of 36 teeth + 6 pairs s/s rails





^{*} Suggested capacity for a correct working

^{**} If the salami kit is not required, please choose another kit from the «equipment available on request» section